SENSORS PX100:40.40.02

PRODUCT DESCRIPTION


The X3 PX100 series of sensors are designed as a conformable and durable sensor for measuring interface pressures. These capacitive sensors were initially designed for medical applications in rehabilitation seating and have since been more widely used in automotive seating, aerospace, research, and product design. The PX100 series of sensors are known for accuracy, durability, and repeatability.

| SENSING | | |
|---------------------|-----------------------------|--------|
| Sensor Technology | Capacitive Pressure Imaging | |
| Pressure Range | 0.2-3.87psi | |
| | 0.14-2.7N/cm ² | |
| Spatial Resolution | 0.5" | 12.7mm |
| Accuracy | ± 10% full scale* | |
| Sampling Frame Rate | 40 frames/s** | |

| PHYSICAL CHARACTERISTICS | | | |
|---|--------------------------|--------------------------|--|
| Total Area | 26.5" x 26.5" | 67.3cm x 67.3cm | |
| Sensing Area | 20" x 20" | 50.8cm x 50.8cm | |
| Thickness (Sensing Area, uncompressed) | 0.03" | 0.08cm | |
| Thickness (Border – cabling side) | 0.04" | 0.1cm | |
| Border Width (cabling side) | 4.5" | 11.4cm | |
| Border Width (non-cabling side) | 2" | 5.1cm | |
| Cable | 46.4" x 2" x 0.16" | 118cm x 5.1cm x 0.4cm | |
| Connector | 4.76" x 2.76" x 0.09" | 12.1cm x 7cm x 0.2cm | |

| SENSING | | |
|---------------------|--------------|--|
| Ambient Temperature | 10°C-40°C | |
| Ambient Humidity | 5% to 90% RH | |

PX100:40.40.02



KEY FEATURES

- High-resolution sensors with a 12.7 mm pitch (resolution) and 1,600 sensing points
- · Very good repeatability
- Low hysteresis and consistent data
- Designed for comfort and healthcare pressure seating applications
- Durable sensor that conforms well to surfaces with a proven track record

REQUIREMENTS FOR OPERATION

- Each PX100:40.40.02 sensor must be connected to one X3 PRO SENSOR PACK
- The X3 PRO SENSOR PACK needs to be connected to an X3 PRO
- The X3 PRO needs to be connected to a power supply and a computer running XSENSOR software to function
- * When verified using the standard XSENSOR verification process.
- **Sampling rate based on using X3 PRO Electronics. Frame rate may vary based on computer configuration.

